Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH500MQMJFK 500 Va Mte CTRL XFRMR 240X480V-120X240V W/Fusing

Hammond Power Solutions

Catalog Number	PH500MQMJFK
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 240X480 PV, 120X240 SV, 500 Kva, Primary and Secondary Fuse Clips Included
Weight per unit	14.2 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

Wattage	500

Descriptions

Description	500 VA MTE CTRL XFRMR 240X480V-120X240V W/FUSING
extra long description	HMND PH500MQMJ-FK CNTL 500VA 240X48
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 240x480 PV, 120x240 SV, 500 kVA, Primary And Secondary Fuse Clips Included
Product Type	CNTL 500VA 240X480-120x240fuse
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS Imperator®
GTIN	00803423081911
Manufacturers Part Number	PH500MQMJ-FK
UPC	803423081911

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Packaging

Carton	1
Weight Per each	14.2

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum