

Commercial Specification Grade Thermoplastic Wallplates

Mid-Size



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

0-22
WALLPLATES

TESTING & CODE COMPLIANCE

- UL 514D and cUL Listed, UL File #E33216
- Meets Federal Specification WP-455
- Meets all CSA requirements, C22.2 no. 42.1, CSA file #9294 (4413-02).

MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, V2 rated. Temperature Rating: -40°C to 70°C.

Commercial Thermoplastic Wallplates


FEATURES

- Mid-Size wallplates are 0.375" (9.53mm) longer and wider on all sides than standard to cover large wallboard openings.
- Assures NEC®-required gap coverage for most wallboard-to-box openings.
- Virtually unbreakable polycarbonate construction – high structural rigidity, long-term form retention.
- Screw-Catch™ feature holds plate mounting screw captive for ease of installation.
- Superior abrasion and impact resistance.
- Color-matched mounting screws captive in 1 and 2 gang plates for faster installation – helps eliminate lost screws on the job.

Combination


2 Gang Toggle Duplex

Color	Catalog No.
Almond	PJ18A
Brown	PJ18B
Black	PJ18BK
Gray	PJ18GY
Red	PJ18RD
Ivory	PJ18V
Light Almond	PJ18LA
White	PJ18W



2 Gang Toggle/Blank (Box-Mounted)

Color	Catalog No.
Almond	PJ113A
Brown	PJ113B
Black	PJ113BK
Gray	PJ113GY
Red	PJ113RD
Ivory	PJ113V
Light Almond	PJ113LA
White	PJ113W



2 Gang Duplex/Blank (Box-Mounted)

Color	Catalog No.
Almond	PJ138A
Brown	PJ138B
Black	PJ138BK
Gray	PJ138GY
Red	PJ138RD
Ivory	PJ138V
Light Almond	PJ138LA
White	PJ138W

