



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLHSWHT12 Rhino 1/2" White Heat Shrink Tubes

Newell (Dymo)

Catalog Number	PLHSWHT12
Manufacturer	Newell (Dymo)
Description	Heat Shrink Tube Label, Heat Type; Polyolefin Material; Black On White Color; 1.5 Meter; UL 224 Approval; 600 Volt Voltage Rating; 0.5 Millimeter Thickness; 257 Deg F Temperature Rating; 3:1 Shrink Ratio; Rohs Compliant; Tube Width 1/2 Inch
Weight per unit	N/A
Product Category	Markers & Marking Tapes

Features

Material	Polyolefin
Shrink Ratio	3:1
Voltage Rating	600 Volt

Material, Color, and Finish

Color	Black on White
-------	----------------

Dimensions and Weight

Length	1.5 Meter
Thickness	0.5 Millimeter

Descriptions

Additional Information	RoHS Compliant; Tube Width 1/2 Inch; Applicable Standard MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Commodity Description	Markers & Marking Tapes
Description	RHINO 1/2" WHITE HEAT SHRINK TUBES
extra long description	HEAT SHRINK TYPE; POLYOLEFIN MATERIAL; BLACK ON WHITE COLOR; 5 FOOT; RHINO 4200 PRINTER TYPE; RHINO[TM] BRAND; ROHS/REACH COMPLIANT; WIDTH 1/2 INCH; VOLTAGE RATING 600 VOLT; SHRINK RATIO 3:1; THICKNESS 0.5 MILLIMETER; TEMPERATURE RATING 257 DEG F; APPLICATION INDUSTRIAL; APPLICABLE STANDARD UL 224, MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Long Description	HEAT SHRINK TUBE LABEL, HEAT TYPE; POLYOLEFIN MATERIAL; BLACK ON WHITE COLOR; 1.5 METER; UL 224 APPROVAL; 600 VOLT VOLTAGE RATING; 0.5 MILLIMETER THICKNESS; 257 DEG F TEMPERATURE RATING; 3:1 SHRINK RATIO; ROHS COMPLIANT; TUBE WIDTH 1/2 INCH
Product Type	Heat Shrink Tube Label



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	DYMO
GTIN	00071701180551
Manufacturers Part Number	18055
UPC	071701180551

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	HEAT

Packaging

Carton	1
Package	5
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 224
Temperature Rating	257 Deg F