



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PLHSWHT14 Rhino 1/4" White Heat Shrink Tubes

*Newell (Dymo)*

Catalog Number	PLHSWHT14
Manufacturer	Newell (Dymo)
Description	Heat Shrink Tube Label, Heat Type; Polyolefin Material; Black On White Color; 1.5 Meter; UL 224 Approval; 600 Volt Voltage Rating; 0.5 Millimeter Thickness; 257 Deg F Temperature Rating; 3:1 Shrink Ratio; Rohs Compliant; Tube Width 1/4 Inch
Weight per unit	N/A
Product Category	Markers & Marking Tapes

### Features

Material	Polyolefin
Shrink Ratio	3:1
Voltage Rating	600 Volt

### Material, Color, and Finish

Color	Black on White
-------	----------------

### Dimensions and Weight

Length	1.5 Meter
Thickness	0.5 Millimeter

### Descriptions

Additional Information	RoHS Compliant; Tube Width 1/4 Inch; Applicable Standard MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Commodity Description	Markers & Marking Tapes
Description	RHINO 1/4" WHITE HEAT SHRINK TUBES
extra long description	HEAT TYPE; BLACK ON WHITE COLOR; UL 224 APPROVAL; 3:1 SHRINK RATIO; TUBE WIDTH 1/4 INCH; APPLICABLE STANDARD ROHS, MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5
Long Description	HEAT SHRINK TUBE LABEL, HEAT TYPE; POLYOLEFIN MATERIAL; BLACK ON WHITE COLOR; 1.5 METER; UL 224 APPROVAL; 600 VOLT VOLTAGE RATING; 0.5 MILLIMETER THICKNESS; 257 DEG F TEMPERATURE RATING; 3:1 SHRINK RATIO; ROHS COMPLIANT; TUBE WIDTH 1/4 INCH
Product Type	Heat Shrink Tube Label

### Manufacturer Information

Brand	DYMO
GTIN	00071701180513
Manufacturers Part Number	18051
UPC	071701180513



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... HEAT/COLD SHRINK .....

Type ..... HEAT .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 0 .....

## Uses, Certifications, and Standards

Approval ..... UL 224 .....

Temperature Rating ..... 257 Deg F .....