



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PLT2MM0 8" 18LB BLK CBL Tie *Panduit Corporation*

Catalog Number	PLT2MM0
Manufacturer	Panduit Corporation
Description	Panduit PLT2M-M0 Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Miniature Cross Section, 8.0" (203MM) Length. For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 1000.
Weight per unit	1.4 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	18

### Dimensions and Weight

Length	8
Thickness	0.05

### Descriptions

Description	8" 18LB BLK CBL TIE
extra long description	PAN PLT2M-M0 Pan-Ty® PLT2M-M0 Cable
Long Description	Panduit PLT2M-M0 Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Miniature cross section, 8.0" (203mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 1000.
Product Type	Pan-Ty® PLT2M-M0 Cable Tie, Black, Uv PA6.6, 8"L, 18LB, PK10
Special Features	Indoor/Outdoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983540273
Manufacturers Part Number	PLT2M-M0
UPC	074983540273

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1000
Package	5000
Weight Per each	1.4

## Uses, Certifications, and Standards

standard	CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant
----------	---