



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

PLT2SM3 7.4" Org Nyl CBL Tie *Panduit Corporation*

Catalog Number	PLT2SM3
Manufacturer	Panduit Corporation
Description	Panduit PLT2S-M3 Locking Cable Ties Are Designed to Satisfy The Needs Of Mil Spec Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Standard Cross Section, 7.4" (188MM) Length. Made Of Nylon 6.6, Are Orange In Color and Come In Packages Of 1000.
Weight per unit	0.0028 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	7.4
Thickness	0.06
Width	NA

Descriptions

Description	7.4" ORG NYL CBL TIE
extra long description	PAN PLT2S-M3 Pan-Ty® PLT2S-M3 Cable
Long Description	Panduit PLT2S-M3 Locking Cable Ties are designed to satisfy the needs of mil spec applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Standard cross section, 7.4" (188mm) length. Made of Nylon 6.6, are orange in color and come in packages of 1000.
Product Type	Pan-Ty® PLT2S-M3 Cable Tie, Orange, PA6.6, 7.4"L, 50LB, PK10
Special Features	Indoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983549191
Manufacturers Part Number	PLT2S-M3
UPC	074983549191

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 1000

Packaging

Carton 1

Package 5000

Weight Per each 0.0028

Uses, Certifications, and Standards

standard CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant
(Type 2S, 21S), RoHS Compliant