



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLT3SM0 11.5" 50LB BLK CBL Tie *Panduit Corporation*

Catalog Number	PLT3SM0
Manufacturer	Panduit Corporation
Description	PLT3S-M0 Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Standard Cross Section, 11.5" (292MM) Length. For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 1000.
Weight per unit	0.0051 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	11.5
Thickness	0.06

Descriptions

Description	11.5" 50LB BLK CBL TIE
extra long description	PAN PLT3S-M0 Pan-Ty® PLT3S-M0 Cable
Long Description	PLT3S-M0 Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Standard cross section, 11.5" (292mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 1000.
Product Type	Pan-Ty® PLT3S-M0 Cable Tie, Black, Uv PA6.6, 11.5"L, 50LB, P
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983540624
Manufacturers Part Number	PLT3S-M0
UPC	074983540624

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1000
Package	2000
Weight Per each	0.005144

Uses, Certifications, and Standards

standard	CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant (Type 2S, 21S), RoHS Compliant
----------	---