



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PLT4HLO 14.5 BLK LCK Ty WRP *Panduit Corporation*

Catalog Number	PLT4HLO
Manufacturer	Panduit Corporation
Description	Panduit PLT4H-L0 Locking Cable Ties Are Designed to Satisfy The Needs Of General Applications, While Delivering Consistent Performance and Reliability. Featuring A Curved Tip to Allow For Easy Pick Up From Flat Surfaces and Faster Initial Threading. Light-Heavy Cross Section, 14.5" (368MM) Length. For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 50.
Weight per unit	0.1400 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	120

### Dimensions and Weight

Length	14.5
Thickness	0.08

### Descriptions

Description	14.5 BLK LCK TY WRP
extra long description	PAN PLT4H-L0 Pan-Ty® PLT4H-L0 Cable
Long Description	Panduit PLT4H-L0 Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Light-heavy cross section, 14.5" (368mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 50.
Product Type	Pan-Ty® PLT4H-L0 Cable Tie, Black, Uv PA6.6, 14.5"L, 120LB,
Special Features	Indoor/Outdoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983540921
Manufacturers Part Number	PLT4H-L0
UPC	074983540921

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 50

Package ..... 500

Weight Per each ..... 0.14

## Uses, Certifications, and Standards

standard ..... CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant  
(Type 2, 21), RoHS Compliant