



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1038RL 10-12AWG 3/8"STD Ylw Insldt RNG TRML *Panduit Corporation*

Catalog Number	PN1038RL
Manufacturer	Panduit Corporation
Description	The PN10-38R-L Pan-Term® Terminal Is A Nylon Insulated, Ring Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.3150 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
media	Yes
Voltage Rating	600

Descriptions

Description	10-12AWG 3/8"STD YLW INSLTD RNG TRML
extra long description	PAN PN10-38R-L Pan-Term® PN10-38R-L
Long Description	The PN10-38R-L Pan-Term® Terminal is a nylon insulated, ring terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN10-38R-L Ring Terminal, Yellow, Nylon, 10-12 Awg

Manufacturer Information

Brand	PANDUIT
GTIN	00074983800384
Manufacturers Part Number	PN10-38R-L
UPC	074983800384

Packaging

Carton	50
Weight Per each	0.315

Uses, Certifications, and Standards

Enclosure	Ring shape
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)