



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PN108FL #10 Nyl FK Term *Panduit Corporation*

Catalog Number	PN108FL
Manufacturer	Panduit Corporation
Description	The PN10-8F-L Pan-Term® Terminal Is A Nylon Insulated, Fork Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0006 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#10

### Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

### Dimensions and Weight

Size	#8
------	----

### Descriptions

Description	#10 NYL FK TERM
extra long description	PAN PN10-8F-L Pan-Term® PN10-8F-L F
Long Description	The PN10-8F-L Pan-Term® Terminal is a nylon insulated, fork terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN10-8F-L Fork Terminal, Yellow, Nylon, 10-12 Awg,

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983803187
Manufacturers Part Number	PN108FL
UPC	074983803187



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Fork Terminal

## Packaging

Carton ..... 50

Package ..... 250

Weight Per each ..... 0.0006

## Uses, Certifications, and Standards

Enclosure ..... Fork shape

Mounting ..... 9/32

standard ..... UL Listed 587H E52164; CSA Certified LR31212

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)