



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN148RC Pan-Term PN14-8R-C Ring Terminal, Blue, *Panduit Corporation*

Catalog Number	PN148RC
Manufacturer	Panduit Corporation
Description	The PN14-8R-C Pan-Term® Terminal Is A Nylon Insulated, Ring Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2900 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
media	Yes
Voltage Rating	600

Descriptions

Description	PAN-TERM PN14-8R-C RING TERMINAL, BLUE,
extra long description	PAN PN14-8R-C Pan-Term® PN14-8R-C R
Long Description	The PN14-8R-C Pan-Term® Terminal is a nylon insulated, ring terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN14-8R-C Ring Terminal, Blue, Nylon, 14-18 Awg, #

Manufacturer Information

Brand	PANDUIT
GTIN	00074983800186
Manufacturers Part Number	PN14-8R-C
UPC	074983800186

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	100
Weight Per each	0.29

Uses, Certifications, and Standards

Enclosure	Ring shape
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)