

Eaton PRL2A3600X42CL

Catalog Number: PRL2A3600X42CL

Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V,
Three-phase, 4W, 600A, 42 circuit, Copper bus

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Pow-R-Stock PRL2A panelboard	PRL2A3600X42CL
UPC	Product Length/Depth
786687011125	85 in
Product Height	Product Width
7 in	18 in
Product Weight	Compliances
75 lb	NEMA Compliant
Certifications	
UL 67	

Product specifications

Type

PRL2A Panelboard

Amperage Rating

600A

Bus material

Copper

Bus Rating

600 A

Feed type

Top/bottom

Number of circuits

42

Number Of Poles

Single-pole, three-pole

Operating Temperature

40°C

Phase

Three-phase

Short-circuit rating

35 A

Wire size

#4 AWG-350 kcmil

Circuit breaker rating

NEMA

Current - max

600 A

NEMA rating

NEMA 1, NEMA 3R

Series

PRL2a

Voltage - max

480 V

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - PRL2A3600X42CL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)