



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC3I 20A 120/277VAC B+S Wire 3W SW Iv *Pass & Seymour/Legrand*

Catalog Number	PS20AC3I
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Ivory, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.22 LB
Weight per unit	0.2240 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Three pole
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
insulation	False
Poles	3-way
Switch Type	Toggle
Voltage	120.0 V
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE 3W SW IV
extra long description	P&S PS20AC3I 20A 120/277VAC B+S WIR

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195408
Manufacturers Part Number	PS20AC3I
UPC	785007195408

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	TOGGLE SWITCH

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.224

Uses, Certifications, and Standards

Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC