



EXTRA HEAVY-DUTY SPEC. GRADE & SECURITY SWITCHES

PS20AC4KL | [Pass & Seymour](#)

FEATURES & BENEFITS

4way Key Lock Back & Side Wire 20amp 120/277volt

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

SPECIFICATIONS

GENERAL INFO

Type: Security Switches
Duty: Extra Heavy Duty
Number Of Poles: 4-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.281"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 20A
Volts: 120/277VAC
Volts (AC): 120/277
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





EXTRA HEAVY-DUTY SPEC. GRADE & SECURITY SWITCHES

PS20AC4KL | [Pass & Seymour](#)

FEATURES & BENEFITS

4way Key Lock Back & Side Wire 20amp 120/277volt

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

SPECIFICATIONS

GENERAL INFO

Type: Security Switches
Duty: Extra Heavy Duty
Number Of Poles: 4-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.281"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 20A
Volts: 120/277VAC
Volts (AC): 120/277
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

