



## INDUSTRIAL EXTRA HEAVY-DUTY SPECIFICATION GRADE SWITCH, WHITE

PS30AC1W | [Pass & Seymour](#)

### FEATURES & BENEFITS

1 Pole Toggle Switch, Back & Side Wire, 30A 120/270Volt, White



- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121507

#### **DIMENSIONS**

Depth (US): 1.073"  
Height (US): 3.281"  
Width (US): 1.320"

#### **TECHNICAL INFORMATION**

Amps: 30A  
Volts: 120/277VAC  
Volts (AC): 120/270  
Grade Type: Industrial

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

