

---

## SERIES 16 IN-LINE CONNECTORS

PS40FBW | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, White

- Thermoplastic elastomer housing for outstanding impact and chemical resistance
- Exceptional seal for maintaining NEMA Type 3R and 4 integrity
- Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product
- Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
- Heavy-duty hex set screws allow greater termination torque
- Copper wire provides quality strain relief
- Copper shim bundles wire strands to reduce "splaying."

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Type: In line connectors female

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: cCSAus File Number LR81290

CSA Standard: Yes

cULus: Yes

UL Listing No: E111198

UL Standard: Yes

UN SPSC: 39121403

#### DIMENSIONS

Length (US): 6.80"

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



