



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS40FRBBL 400A 600V Fmale Cam DSS PNL MT BL

Pass & Seymour/Legrand

Catalog Number	PS40FRBBL
Manufacturer	Pass & Seymour/Legrand
Description	Female Cam Device 400A 600V, Panel Mount, Blue
Weight per unit	0.7600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	400
connection	Double Set Screw
Cord Type	Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only
Material	Nylon
Voltage	600.0 V
Voltage Rating	600
Wire Size	2/0 - 4/0

Dimensions and Weight

Size	Consult the Factory for Dimensional Information
------	---

Descriptions

Description	400A 600V FEMALE CAM DSS PNL MT BL
extra long description	P&S PS40FRBBL 400A 600V FEMALE CAM D
Long Description	Female Cam Device 400A 600V, panel mount, Blue
Product Type	400A 600V Fmale Cam DSS PNL MT Blue
Special Features	Nylon housing provides outstanding impact and chemical resistance. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws (available on double set screw version only) allow greater termination torque.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007308389
Manufacturers Part Number	PS40-FRBBL
UPC	785007308389

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Cam-Type Series 16 Double Set Screw Panel Mount Female

Trade Size

Amperage	400.0
----------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.76

Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
Mounting	PANEL
nema rating	NEMA 3R and 4 for indoor applications
standard	UL, cUL