



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS40MBBK 400A 600V Male Cam Plug BK

*Pass & Seymour/Legrand*

Catalog Number	PS40MBBK
Manufacturer	Pass & Seymour/Legrand
Description	Male Cam Device Plug, 400A 600V, Black
Weight per unit	0.7460 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	400
Cord Type	Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only
Poles	1
Voltage Rating	600
Wire Size	2/0 - 4/0

### Dimensions and Weight

Size	6.875
------	-------

### Descriptions

Description	400A 600V MALE CAM PLUG BK
extra long description	P&S PS40MBBK 400A 600V MALE CAM PLU
Long Description	Male Cam Device Plug, 400A 600V, Black
Product Type	400A 600V Male Cam Plug BK
Special Features	Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim b

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007308051
Manufacturers Part Number	PS40-MBBK
UPC	785007308051

### Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Cam-Type Series 16 In-Line Connector Male



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.746

## Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	Enclosure: NEMA Type 3R and 4;Flammability UL94 V2;Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact
nema rating standard	Enclosure: NEMA Type 3R and 4 UL, cCSAus