



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS5266XHG Straight Blade Plug 3W 15A 125V HG

Pass & Seymour/Legrand

Catalog Number	PS5266XHG
Manufacturer	Pass & Seymour/Legrand
Description	Hospital Grade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 1.516 In;0.230 to 0.690 In (Cord) Diameter, 2.791 In Length, #18 to #10 Awg Wire Size, Chemical Resistant, Impact Resistant, Corrosion Resistant, 0.164 LB
Weight per unit	0.1632 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Wire Grounding
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125

Dimensions and Weight

Size	2.8 in
------	--------

Descriptions

Description	STR BLD PLUG 3W 15A 125V HG
extra long description	P&S PS5266XHG STR BLD PLUG 3W 15A 1

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007236774
Manufacturers Part Number	PS5266XHG
UPC	785007236774

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Hospital Grade Plug Straight Blade

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Package	50
Weight Per each	0.1632

Uses, Certifications, and Standards

standard	FEDSPEC, CULUS, UL 498
----------	------------------------