



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PS5266XHG Straight Blade Plug 3W 15A 125V HG

*Pass & Seymour/Legrand*

Catalog Number	PS5266XHG
Manufacturer	Pass & Seymour/Legrand
Description	Hospital Grade Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 1.516 In;0.230 to 0.690 In (Cord) Diameter, 2.791 In Length, #18 to #10 Awg Wire Size, Chemical Resistant, Impact Resistant, Corrosion Resistant, 0.164 LB
Weight per unit	0.1632 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	15
connection	Wire Grounding
Poles	2
Voltage	125.0 V
Voltage Rating	125

### Dimensions and Weight

Size	2.8 in
------	--------

### Descriptions

Description	STR BLD PLUG 3W 15A 125V HG
extra long description	P&S PS5266XHG STR BLD PLUG 3W 15A 1

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007236774
Manufacturers Part Number	PS5266XHG
UPC	785007236774

### Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Hospital Grade Plug Straight Blade

### Trade Size

Amperage	15.0
----------	------

### Packaging

Carton	10
Package	50
Weight Per each	0.1632

### Uses, Certifications, and Standards

standard	FEDSPEC, CULUS, UL 498, FEDSPEC
----------	---------------------------------