

---

## 15A, 125V EXTRA-HARD USE HOSPITAL- GRADE CONNECTOR, BLACK & CLEAR

PS5269XHG | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Straight Blade Connector 2pole 3wire 15amp 125volt Hospital Grade



- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
UL Listing No: No  
UN SPSC: 39121402  
UR: No

## DIMENSIONS

Depth (US): 2.638"

Height (US): 1.516"

Width (US): 1.516"

## TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



---

## 15A, 125V EXTRA-HARD USE HOSPITAL- GRADE CONNECTOR, BLACK & CLEAR

PS5269XHG | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Straight Blade Connector 2pole 3wire 15amp 125volt Hospital Grade



- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
UL Listing No: No  
UN SPSC: 39121402  
UR: No

## DIMENSIONS

Depth (US): 2.638"

Height (US): 1.516"

Width (US): 1.516"

## TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

