



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS8300HLA Hosp Grad Duplex Recp 20A 125VAC La

Pass & Seymour/Legrand

Catalog Number	PS8300HLA
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.2105 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.780

Descriptions

Description	HOSP GRAD DUPLEX RECP 20A 125VAC LA
extra long description	P&S PS8300HLA HOSP GRAD DUP RECEPT
Long Description	Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Hosp Grad Dup Recept 20A 125VAC La
Special Features	Heavy-duty, brass strap for added strength and ground conductivity. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around face to prevent strap from separating from face and back body. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Two drive screws anchor strap to back body and face. Tri-drive brass terminal screws. Internal screw-presure-plate back and side wire capability. Two back wire holes for more wiring flexibili



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007860061
Manufacturers Part Number	PS8300-HLA
UPC	785007860061

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2105

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC
Temperature Rating	-40° - 60° C