

Eaton PSG60F24RM

Catalog Number: PSG60F24RM

Eaton PSG series Power Supply, Aluminum, 320-575 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 960W output power, -25°C-75°C operating temp



General specifications

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG60F24RM
	UPC
	786685683577
Product Length/Depth	Product Height
7 in	3 in
Product Width	Product Weight
6.5 in	4 lb
Warranty	Compliances
3 year	RoHS Compliant
	CE Marked

Certifications

UL 508
IEC Rated
CSA Std. C22.2
EN Listed

Operating temperature - max

75 °C

Operating temperature - min

-25 °C

Phase

Three-phase

Frequency rating

47-63 Hz

Enclosure color

Aluminum

Output voltage

24 V

Terminals

Finger-safe

Input voltage

320-575 Vac

Output

960 W

Brochures

Eaton's PSG Series Power Supplies

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Drawings

PSG60F24RM 3D Model Xchange

PSG60F24RM 2D PDF

PSG60F24RM 2D Drawing Xchange

PSG60F24RM 3D Inventor

PSG60F24RM AutoCAD 2D Footprint

PSG60F24RM AutoCAD 2D Footprint (mm)

Installation instructions

Installation Instructions for PSG60F Power Supply

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - PSG60F24RM



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia