



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT8300W Hosp GRD Ehd Duplex Recp 20A/125V WH

Pass & Seymour/Legrand

Catalog Number	PT8300W
Manufacturer	Pass & Seymour/Legrand
Description	Plugtail Registered Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V Plugtail Registered Devices and Connectors Mean That Device Installation Is The Same Regardless Of Skill Level Of The Installer. The UI-Listed Connectors Are Keyed to Ensure Proper Wiring Installation Into Each Receptacle.
Weight per unit	0.2264 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	12

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	3.281
Width	.866



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	HOSP GRD EHD DUPLEX RECP 20A/125V WH
extra long description	P&S PT8300W HOSP GRD EHD DUP RECEPT
Long Description	PlugTail Registered Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.
Product Type	Hosp GRD Ehd Dup Recept 20A/125V WH
Special Features	Exclusive patented feature, circuit label on face allows permanent circuit identification. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007091168
Manufacturers Part Number	PT8300-W
UPC	785007091168

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2264

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, cULus UL498, FEDSPEC