



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1010RL 12-10 Vinyl Ins Ring Terminal Ylw # 10 Stud *Panduit Corporation*

Catalog Number	PV1010RL
Manufacturer	Panduit Corporation
Description	The PV10-10R-L Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. Extended Barrel Insulation Provides Protection and Strain Relief When Crimped.
Weight per unit	0.2400 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	12-10 VINYL INS RING TERMINAL YLW # 10 STUD
extra long description	PAN PV10-10R-L Pan-Term® PV10-10R-L
Long Description	The PV10-10R-L Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength. Extended barrel insulation provides protection and strain relief when crimped.
Product Type	Pan-Term® PV10-10R-L Ring Terminal, Yellow, Vinyl, 10-12 Awg



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983801329
Manufacturers Part Number	PV10-10R-L
UPC	074983801329

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Package	500
Weight Per each	0.24

Uses, Certifications, and Standards

Enclosure	Ring shape
Mounting standard	5/16 cULus Listed 587H E52164, CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)