



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV106LFL 12-10 Vnyl Ins LCKNG FRK Term Ylw # 6 Stud *Panduit Corporation*

Catalog Number	PV106LFL
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Vinyl Insulated, Funnel Entry, Butted Seam, 12- 10 Awg, #6 Stud Size, Standard Package.
Weight per unit	0.2400 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	#6
------	----

Descriptions

Description	12-10 VNYL INS LCKNG FRK TERM YLW # 6 STUD
extra long description	PAN PV10-6LF-L Pan-Term® PV10-6LF-L
Long Description	Locking Fork Terminal, vinyl insulated, funnel entry, butted seam, 12- 10 AWG, #6 stud size, standard package.
Product Type	Pan-Term® PV10-6LF-L Loose Piece Terminal

Manufacturer Information

Brand	PANDUIT
GTIN	00074983808120
Manufacturers Part Number	PV10-6LF-L
UPC	074983808120

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Availability

minimum qty	50
-------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Package	500
Weight Per each	0.24

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	UL Listed 587H E52164; CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)