



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV146FC Fork Terminal *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV146FC |
| Manufacturer | Panduit Corporation |
| Description | The PV14-6F-C Pan-Term® Terminal Is A Vinyl Insulated, Fork Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------|
| connection | Funnel |
| insulation | Vinyl |
| Material | Copper |
| media | Yes |
| Voltage Rating | 600 |
| Wire Size | #14 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Blue |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #6 |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | FORK TERMINAL |
| extra long description | PAN PV14-6F-C Pan-Term® PV14-6F-C F |
| Long Description | The PV14-6F-C Pan-Term® Terminal is a vinyl insulated, fork terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® PV14-6F-C Fork Terminal, Blue, Vinyl, 14-16 Awg, # |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983804061 |
| Manufacturers Part Number | PV14-6F-C |
| UPC | 074983804061 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Fork Terminal |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----|
| Carton | 100 |
| Package | 500 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure | Fork shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164; CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |