



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV146LFM 18-14AWG Vnyl Ins LCKNG FRK Term BL #6 Stud *Panduit Corporation*

Catalog Number	PV146LFM
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Vinyl Insulated, Funnel Entry, 18- 14 Awg, #6 Stud Size, Bulk Package.
Weight per unit	0.0023 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Tin-Plated

Dimensions and Weight

Size	#6
------	----

Descriptions

Description	18-14AWG VNYL INS LCKNG FRK TERM BL #6 STUD
extra long description	PAN PV14-6LF-M Pan-Term® PV14-6LF-M
Long Description	Locking Fork Terminal, vinyl insulated, funnel entry, 18- 14 AWG, #6 stud size, bulk package.
Product Type	Pan-Term® PV14-6LF-M Fork Terminal, Blue, Vinyl, 14-18 Awg,

Manufacturer Information

Brand	Panduit®
GTIN	00074983808076
Manufacturers Part Number	PV14-6LF-M
UPC	074983808076

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Ring Terminal

Packaging

Carton	1000
Weight Per each	0.0023



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	UL Listed 587H E52164; CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)