



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV148FC Fork Terminal *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | PV148FC |
| Manufacturer | Panduit Corporation |
| Description | The PV14-8F-C Pan-Term® Terminal Is A Vinyl Insulated, Fork Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------|
| connection | Funnel |
| insulation | Vinyl |
| Material | Copper |
| media | Yes |
| Voltage Rating | 600 |
| Wire Size | 14 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Blue |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #8 |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | FORK TERMINAL |
| extra long description | PAN PV14-8F-C Pan-Term® PV14-8F-C F |
| Long Description | The PV14-8F-C Pan-Term® Terminal is a vinyl insulated, fork terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® PV14-8F-C Fork Terminal, Blue, Vinyl, 14-16 Awg, # |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983804085 |
| Manufacturers Part Number | PV14-8F-C |
| UPC | 074983804085 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 100

Package 500

Weight Per each 1

Uses, Certifications, and Standards

Enclosure Fork shape

Mounting 5/16

standard CSA Certified LR31212;UL Listed 587H E52164

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)