



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV1510CT00 1-1/2IN PVC Coated Galv Rigid Cond 10'

*Calpipe Industries, Inc*

Catalog Number	PV1510CT00
Manufacturer	Calpipe Industries, Inc
Description	Rigid Conduit, Steel Material; Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; 10 Foot; 1.624 Inch Inner Diameter; 1.98 Inch Outer Diameter; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard
Weight per unit	N/A
Product Category	20220415171916

### Features

Applicable Standard	ANSI C80.1, NEMA RN-1
End Style	Threaded
Material	Steel
Wall Thickness	0.138 INCH

### Material, Color, and Finish

Finish	Hot Dip Galvanized, 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--

### Dimensions and Weight

Inner Diameter	1.624 INCH
Length	10 Foot
Outer Diameter	1.98 INCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Constructional Feature Corrosion Resistant; Includes Coupling; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mil
Commodity Description	Pvc Schedule 40 Conduit
Description	1-1/2IN PVC COATED GALV RIGID COND 10'
extra long description	STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 1.624 INCH INNER DIAMETER; 1.98 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 281 POUND PER 100 FOOT WEIGHT; 380 FOOT PER BUNDLE STANDARD PACKAGE; 1-1/2 INCH TRADE SIZE; 0.138 INCH WALL THICKNESS; THREADED END STYLE; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; INCLUDES COUPLING; PV MODEL
Long Description	RIGID CONDUIT, STEEL MATERIAL; HOT DIP GALVANIZED, 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; 10 FOOT; 1.624 INCH INNER DIAMETER; 1.98 INCH OUTER DIAMETER; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD
Product Type	Rigid Conduit

## Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656075194
Manufacturers Part Number	PV1510CT00
Model	PV
UPC	847656075194

## Trade Size

Trade Size	1-1/2 INCH
------------	------------

## Packaging

Carton	1
Standard Package	380 Foot per Bundle
Weight	281 Pound per 100 Foot
Weight Per each	0

## Uses, Certifications, and Standards

Approval	UL 6, CUL
----------	-----------