



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV1810FCY Pan-Term® PV18-10F-Cy For Panduit Corporation

Catalog Number	PV1810FCY
Manufacturer	Panduit Corporation
Description	The PV18-10F-Cy Pan-Term® Terminal Is A Vinyl Insulated, Fork Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.3000 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#16

### Material, Color, and Finish

Color	Red
Finish	Tinned

### Dimensions and Weight

Size	#10
------	-----

### Descriptions

Description	PAN-TERM® PV18-10F-CY FOR
extra long description	PAN PV18-10F-CY Pan-Term® PV18-10F-
Long Description	The PV18-10F-CY Pan-Term® Terminal is a vinyl insulated, fork terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV18-10F-Cy Fork Terminal, Red, Vinyl, 16-22 Awg,

### Manufacturer Information

Brand	Panduit®
GTIN	00074983686490
Manufacturers Part Number	PV18-10F-CY
UPC	074983686490

### Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Package	500
Weight Per each	0.3

## Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	5/16
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)