



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV188FCY Pan-Term® PV18-8F-Cy Fork *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | PV188FCY |
| Manufacturer | Panduit Corporation |
| Description | The PV18-8F-Cy Pan-Term® Terminal Is A Vinyl Insulated, Fork Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 0.2800 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------|
| connection | Funnel |
| insulation | Vinyl |
| Material | Copper |
| media | Yes |
| Voltage Rating | 600 |
| Wire Size | #16 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Red |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #8 |
|------|----|

Descriptions

| | |
|------------------------|---|
| Description | PAN-TERM® PV18-8F-CY FORK |
| extra long description | PAN PV18-8F-CY Pan-Term® PV18-8F-CY |
| Long Description | The PV18-8F-CY Pan-Term® Terminal is a vinyl insulated, fork terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® PV18-8F-Cy Fork Terminal, Red, Vinyl, 16-22 Awg, # |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983694693 |
| Manufacturers Part Number | PV18-8F-CY |
| UPC | 074983694693 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | TERMINALS |
| Type | Fork Terminal |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Package | 500 |
| Weight Per each | 0.28 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure | Fork shape |
| Mounting | 5/16 |
| standard | UL Listed 587H E52164; CSA Certified LR31212 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |