

# Eaton QB1030GF

Catalog Number: QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QB1030GF
<b>UPC</b>	<b>Product Length/Depth</b>
786680222429	4 in
<b>Product Height</b>	<b>Product Width</b>
1 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	UL 489

Photo is representative

## Physical Attributes

### Circuit breaker type

QB

### Connection

Bolt-on

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-4 AWG

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QB1030GF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QB1030GF

Catalog Number: QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QB1030GF
<b>UPC</b>	<b>Product Length/Depth</b>
786680222429	4 in
<b>Product Height</b>	<b>Product Width</b>
1 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	UL 489

Photo is representative

## Physical Attributes

### Circuit breaker type

QB

### Connection

Bolt-on

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-4 AWG

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QB1030GF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)