

Specifications

Eaton QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB



Photo is representative



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QB1030GF
UPC	786680222429
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	1 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL 489



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QB
CONNECTION	Bolt-on
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-4 AWG

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - QB1030GF](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications

Eaton QB1030GF

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, Bolt-on, #14-4 AWG, QB



Photo is representative



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QB1030GF
UPC	786680222429
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	1 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	UL 489

Physical Attributes

CIRCUIT BREAKER TYPE	QB
CONNECTION	Bolt-on
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-4 AWG

Performance Ratings

AMPERAGE RATING	30 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - QB1030GF](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

