


QB2B

Twin 75 watt Quartz Bullet floods come pre-assembled and pre-wired on C103 Mounting plate. Lamps supplied.

Color: Black

Weight: 2.1 lbs



Lamp Info

Type: T-4
 Watts: 75W
 Shape/Size: N/A
 Base: N/A
 ANSI: N/A
 Hours: 1,500
 Lamp Lumens: 1,500
 Efficacy: 20 LPW

Ballast Info

Type: N/A
 120V: N/A
 208V: N/A
 240V: N/A
 277V: N/A
 Input Watts: 75W
 Efficiency: 100%

Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping.

Reflector:

Semi-specular anodized aluminum.

Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

Lens:

Thick, tempered glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Replacement Lamps:

.

Installation:

Twin 75w Flood Kit pre-assembled on C103 plate for easy installation.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.