

# Specifications

## Eaton QBGFEP2015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 15A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2015
UPC	786679473474
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.66 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

### Performance Ratings

AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	30 mA trip sensitivity

<b>VOLTAGE RATING</b>	120/240 V
-----------------------	-----------

## Miscellaneous

<b>SPECIAL FEATURES</b>	Bolt-on mounting
-------------------------	------------------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFEP2015</a>
--------------------------------------	--

<b>PROJECT NAME:</b>
----------------------

<b>PROJECT NUMBER:</b>
------------------------

<b>PREPARED BY:</b>
---------------------

<b>DATE:</b>
--------------



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QBGFEP2015



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 15A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEF2015
UPC	786679473474
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.66 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE	QBGFEF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

### Performance Ratings

AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	30 mA trip sensitivity

<b>VOLTAGE RATING</b>	120/240 V
-----------------------	-----------

## Miscellaneous

<b>SPECIAL FEATURES</b>	Bolt-on mounting
-------------------------	------------------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFEP2015</a>
--------------------------------------	--

<b>PROJECT NAME:</b>
----------------------

<b>PROJECT NUMBER:</b>
------------------------

<b>PREPARED BY:</b>
---------------------

<b>DATE:</b>
--------------



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

