## **Specifications**



## Eaton QBGFEP2015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 15A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

General specifications	
PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2015
UPC	786679473474
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.66 lb
WARRANTY	1 year
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



<b>Physical Attributes</b>	
CIRCUIT BREAKER TYPE	QBGFEP
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
ТҮРЕ	Ground fault circuit breaker

<b>Performance Ratings</b>	
AMPERAGE RATING	15 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	30 mA trip sensitivity

VOLTAGE RATING	120/240 V

Miscellaneous		Resources
SPECIAL FEATURES	Bolt-on mounting	SPECIFICATIONS AND DATASHEETS

**PROJECT NAME:** PROJECT NUMBER: PREPARED BY: DATE:



**Eaton Corporation plc** 

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Eaton Specification Sheet -

OBGFEP2015









