

Specifications

Eaton QBGFEP2040

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,40A,10 kAIC,Two-pole,120/240V,Non-Interchangeable,QBGF



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2040
UPC	786679145180
PRODUCT LENGTH/DEPTH	6.125 in
PRODUCT HEIGHT	2.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.85 lb
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	Bolt-on mounting

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFEP2040

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton QBGFEP2040



Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 40A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFEP2040
UPC	786679145180
PRODUCT LENGTH/DEPTH	6.125 in
PRODUCT HEIGHT	2.25 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.85 lb
CERTIFICATIONS	UL 943
CATALOG NOTES	HACR rated



Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	40 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	Bolt-on mounting

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFEP2040

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

