

Eaton QBGFEP2050

Catalog Number: QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

General specifications

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2050
UPC	Product Length/Depth
786679145203	5.8 in
Product Height	Product Width
4.4 in	3 in
Product Weight	Warranty
0.9 lb	1 year
Certifications	Catalog Notes
UL 943	HACR rated



Physical Attributes

Circuit breaker type
QBGFEP

Mounting Method
Bolt-on

Number of poles
Two-pole

Type
Ground fault circuit breaker

Performance Ratings

Amperage Rating
50 A

Interrupt rating
10 kAIC

Trip Type
Non-Interchangeable

Trip rating
30 mA trip sensitivity

Voltage rating
120/240 V

Miscellaneous

Special features
Bolt-on mounting

Resources

Brochures
[Loadcenters and Circuit Breakers](#)

Catalogs
[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets
[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)
[Eaton Specification Sheet - QBGFEP2050](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)