

# Eaton QBGFT1015

Catalog Number: QBGFT1015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFT1015
<b>UPC</b>	<b>Product Length/Depth</b>
786680130953	1 in
<b>Product Height</b>	<b>Product Width</b>
1 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	1 year
<b>Certifications</b>	
UL 489	

## Physical Attributes

### Circuit breaker type

QBGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-10 AWG Cu

#12-10 AWG Al

## Performance Ratings

### Amperage Rating

15 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBGFT1015](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton QBGFT1015

Catalog Number: QBGFT1015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFT1015
<b>UPC</b>	<b>Product Length/Depth</b>
786680130953	1 in
<b>Product Height</b>	<b>Product Width</b>
1 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	1 year
<b>Certifications</b>	
UL 489	

## Physical Attributes

### Circuit breaker type

QBGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#14-10 AWG Cu

#12-10 AWG Al

## Performance Ratings

### Amperage Rating

15 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - QBGFT1015](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)