

# Specifications

## Eaton QBGFT2020



Photo is representative

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14-10 Cu, #12-10 Al, QBGF

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2020
UPC	786676026710
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
----------------------	------

### Performance Ratings

AMPERAGE RATING	20 A
-----------------	------

<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#14-10 AWG Cu #12-10 AWG Al

<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Common trip
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

Miscellaneous	
<b>SPECIAL FEATURES</b>	5 mA Trip Sensitivity

Resources	
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFT2020</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

