

# Eaton QBGFT2030

Catalog Number: QBGFT2030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #10 Cu, #8 Al, QBGF

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton QB GFCI circuit breaker	QBGFT2030
<b>UPC</b>	<b>Product Length/Depth</b>
786676026734	4.5 in
<b>Product Height</b>	<b>Product Width</b>
2 in	2.75 in
<b>Product Weight</b>	<b>Warranty</b>
0.6 lb	1 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	HACR rated

## Physical Attributes

**Circuit breaker type**  
QBGF

**Mounting Method**  
Bolt-on

**Number of poles**  
Two-pole

**Type**  
Ground fault circuit breaker

**Wire size**  
#10 Cu, #8 Al

## Performance Ratings

**Amperage Rating**  
30 A

**Interrupt rating**  
10 kAIC

**Trip Type**  
Common trip

**Trip rating**  
5 mA trip sensitivity

**Voltage rating**  
120/240 V

## Miscellaneous

**Special features**  
5 mA Trip Sensitivity

## Resources

**Brochures**  
[Loadcenters and Circuit Breakers](#)

**Specifications and datasheets**  
[Eaton Specification Sheet - QBGFT2030](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)