

Eaton QBGFT2040

Catalog Number: QBGFT2040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8 Cu, #8-6 Al, QBGF

General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFT2040
UPC	Product Length/Depth
786676026741	4.5 in
Product Height	Product Width
2 in	2.75 in
Product Weight	Warranty
0.6 lb	1 year
Certifications	Catalog Notes
UL 489	HACR rated

Physical Attributes

Circuit breaker type

QBGF

Mounting Method

Bolt-on

Number of poles

Two-pole

Type

Ground fault circuit breaker

Wire size

#8 Cu

#8–6 Al

Performance Ratings

Amperage Rating

40 A

Interrupt rating

10 kAIC

Trip Type

Common trip

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

5 mA Trip Sensitivity

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBGFT2040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)