## **Specifications**



Photo is representative

## Eaton QBGFT2040

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 40A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8 Cu, #8–6 Al, QBGF

General specifications	
PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2040
UPC	786676026741
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



Physical Attributes		
CIRCUIT BREAKER TYPE	QBGF	

Performance Ratings	
AMPERAGE RATING	40 A

MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
ТҮРЕ	Ground fault circuit breaker
WIRE SIZE	#8 Cu #8–6 Al

INTERRUPT RATING	10 kAIC
TRIP TYPE	Common trip
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT2040

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



## **Eaton Corporation plc**

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

product and support information.

All other trademarks are property of their respective owners

Follow us on social media to get the latest









