

Eaton QBH1020GF

Catalog Number: QBH1020GF

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,Bolt-on mounting,20A,22kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB

General specifications



Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBH1020GF

UPC

786680222450

Product Length/Depth

3.5 in

Product Height

1.3 in

Product Width

6 in

Product Weight

0.47 lb

Warranty

1 year

Compliances

Contact Manufacturer

Certifications

UL 489

Physical Attributes

Circuit breaker type

QB

Connection

Bolt-on

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Ground fault circuit breaker

Wire size

#14-4 AWG

Performance Ratings

Amperage Rating

20 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Trip rating

5 mA trip sensitivity

Voltage rating

120/240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - QBH1020GF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia