

Specifications

Eaton QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF



Photo is representative



General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBHGFT2020
UPC	786676027823
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.6 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated

Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
VOLTAGE RATING	120/240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHGFT2020
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

