

Eaton QBHW1040

Catalog Number: QBHW1040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 40A, 22 kAIC, 120/240V

General specifications



| | |
|-------------------------------------------|----------------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW1040 |
| | UPC |
| | 786679392256 |
| Product Length/Depth | Product Height |
| 3.6 in | 4.7 in |
| Product Width | Product Weight |
| 1.2 in | 0.3 lb |
| Warranty | Certifications |
| 1 year | UL Listed CSA Certified |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag

Performance Ratings

Amperage Rating

40 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBHW1040

Catalog Number: QBHW1040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 40A, 22 kAIC, 120/240V

General specifications



| | |
|-------------------------------------------|----------------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW1040 |
| | UPC |
| | 786679392256 |
| Product Length/Depth | Product Height |
| 3.6 in | 4.7 in |
| Product Width | Product Weight |
| 1.2 in | 0.3 lb |
| Warranty | Certifications |
| 1 year | UL Listed CSA Certified |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag

Performance Ratings

Amperage Rating

40 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1040](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)