

Eaton QBHW1050

Catalog Number: QBHW1050

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 70 A, 22 kAIC, Single-pole, 120/240 V, Non-interchangeable, QBHW



General specifications

Product Name	Catalog Number
Eaton QB thermal magnetic circuit breaker	QBHW1050
	UPC
	786679392300
Product Length/Depth	Product Height
3.6 in	3.2 in
Product Width	Product Weight
1.2 in	0.35 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

50 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

17

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW1050](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)