

# Specifications

## Eaton QBHW2015

Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 15A, 22 kAIC, 120/240V , Bolt-on



### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW2015
<b>UPC</b>	786679392508
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.1 in
<b>PRODUCT WEIGHT</b>	0.55 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	HACR rated



*Powering Business Worldwide*

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

<b>AMPERAGE RATING</b>	15 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>VOLTAGE RATING</b>	120/240 V

## Miscellaneous

<b>QUANTITY</b>	7
-----------------	---

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBHW2015</a>
--------------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

