

# Specifications

## Eaton QBHW2040

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Two-pole, 40A, 22 kAIC, 120/240V , Bolt-on

### General specifications

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton QB thermal magnetic circuit breaker |
| <b>CATALOG NUMBER</b>       | QBHW2040                                  |
| <b>UPC</b>                  | 786679392751                              |
| <b>PRODUCT LENGTH/DEPTH</b> | 2.9 in                                    |
| <b>PRODUCT HEIGHT</b>       | 2.9 in                                    |
| <b>PRODUCT WIDTH</b>        | 2 in                                      |
| <b>PRODUCT WEIGHT</b>       | 0.65 lb                                   |
| <b>WARRANTY</b>             | 1 year                                    |
| <b>CERTIFICATIONS</b>       | UL Listed<br>CSA Certified                |
| <b>CATALOG NOTES</b>        | HACR rated                                |



### Physical Attributes

|                             |          |
|-----------------------------|----------|
| <b>CIRCUIT BREAKER TYPE</b> | QBHW     |
| <b>MOUNTING METHOD</b>      | Bolt-on  |
| <b>NUMBER OF POLES</b>      | Two-pole |
| <b>TYPE</b>                 | Quicklag |

### Miscellaneous

|                 |   |
|-----------------|---|
| <b>QUANTITY</b> | 7 |
|-----------------|---|

### Performance Ratings

|                         |                     |
|-------------------------|---------------------|
| <b>AMPERAGE RATING</b>  | 40 A                |
| <b>INTERRUPT RATING</b> | 22 kAIC             |
| <b>TRIP TYPE</b>        | Non-Interchangeable |
| <b>VOLTAGE RATING</b>   | 120/240 V           |

### Resources

|                                      |  |
|--------------------------------------|--|
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - QBHW2040</a> |
|--------------------------------------|--|

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

